

CAT. N° 4 117 65

**RCCB TX<sup>3</sup> - 4P 400 V~ - 30 MA - 40 A - A TYPE**

|                           |        |
|---------------------------|--------|
| Pack (number of units)    | 1      |
| Volume (dm <sup>3</sup> ) | 0,701  |
| Weight (g)                | 338,00 |

**Product characteristics****4-pole 400 V~**

- Neutral on right-hand side

**A type**

- Sensitivity : 30 mA
- In : 40 A
- Number of modules : 2

**General characteristics****RCCBs TX<sup>3</sup> residual current circuit breakers - from 16 A to 80 A - AC and A types**

- Conform to IEC 61008-1
- Compatible with prong-type and fork type supply busbars
- AC type : detect AC component faults
- A type : detect AC and DC component faults

**Documentation****Catalogue pages & additional information**

- [Description page \(p.054\)](#)
- [Dimensions of din-rail equipment](#)

**Environmental product profile**

- [Environnemental product sheet n°8 E0013C-EN](#)

**Agreements & certificates of conformity**

- [VDE - 40041196](#)
- [OC / CB - CB FR 705078](#)
- [OC / CB - CB-FR 700757](#)