

CAT. N° 4 117 73



## RCD DX<sup>3</sup>-ID - 4P 400 V~ NEUTRAL RIGHT HAND SIDE - 100 A - 100 MA - A TYPE

|                           |        |
|---------------------------|--------|
| Pack (number of units)    | 1      |
| Volume (dm <sup>3</sup> ) | 0,701  |
| Weight (g)                | 386,00 |

### Product characteristics

4-pole - 400 V~ - neutral on right-hand side

#### A type

- Sensitivity : 100 mA
- In : 100 A
- Number of modules : 4

### General characteristics

#### RCCBs - DX<sup>3</sup>-ID - residual current circuit breakers 16 A to 100 A - AC, A, F and B types

- Conform to IEC 61008 - 1, IEC 62423 (B type and F type)
- Compatible with prong-type and fork type supply busbars
- AC type : detect sinusoidal AC residual currents
- A type : detect sinusoidal AC and pulsating DC residual currents
- F type (High immunity) : detect AC and pulsating DC residual currents
- Enhanced immunity to unwanted tripping in disturbed environments
- Detection of high frequency fault currents
- B type : detect sinusoidal AC, pulsating DC and smooth DC residual currents
- Can be equipped with DX<sup>3</sup> signalling and remote tripping auxiliaries and motorised controls

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.057\)](#)
- [Technical page \(p.058\)](#)
- [Dimensions of din-rail equipment](#)

#### Environmental product profile

- [Environnemental product sheet n°8 E0013C-EN](#)

#### Agreements & certificates of conformity

- [OC / CB - CB-FR\\_700719](#)
- [OC / CB - CB FR\\_705078](#)
- [VDE - 40032162](#)
- [NF - NF012\\_1106](#)