

CAT. N° 4 117 75



RCCB TX³ - 4P 400 V~ - 100 MA - 40 A - A TYPE

Pack (number of units)	1
Volume (dm ³)	0,701
Weight (g)	334,00

Product characteristics

4-pole 400 V~

- Neutral on right-hand side

A type

- Sensitivity : 100 mA
- In : 40 A
- Number of modules : 4

General characteristics

RCCBs TX³ residual current circuit breakers - from 16 A to 80 A - AC and A types

- Conform to IEC 61008-1
- Compatible with prong-type and fork type supply busbars
- AC type : detect AC component faults
- A type : detect AC and DC component faults

Documentation

Catalogue pages & additional information

- [Description page \(p.054\)](#)
- [Dimensions of din-rail equipment](#)

Agreements & certificates of conformity

- [VDE-40041196](#)
- [OC / CB-CB_FR_705078](#)
- [OC / CB-CB-FR_700757](#)

Installation & technical data

- [F01576EN-03](#)

Environmental product profile

- [LGRP-00366-V02](#)