

CAT. N° 4 120 74



THREE-PHASE METER EMDX³ WITH DIRECT CONNECTION - NON-MID - 125 A - RS485 AND PULSE OUTPUTS - 6 MODULES

Pack (number of units)	1
Volume (dm ³)	1,287
Weight (g)	604,00

Product characteristics

Three-phase meters

Direct connection

- Non-MID :
- Maximum current : 125 A
- Output type : Pulse and RS 485
- Dual tariff : Yes
- Number of modules : 6

General characteristics

EMDX³ electrical energy meters - rail mounting

- Measure the electricity consumed by a single-phase or three-phase circuit downstream of the electricity distribution metering
- Display electricity consumption in kWh, as well as other values such as current, active energy, reactive energy and power (depending on the catalogue number)
- Conform to standards IEC 61557-12, IEC 62053-21/23, IEC 62052-11 and IEC 62052-31
- MID compliance ensures accuracy of the metering with a view to recharging for the electricity used

Documentation

Catalogue pages & additional information

- [Description page \(p.102\)](#)
- [Technical page \(p.107\)](#)

Installation & technical data

- [F02548EN-00](#)
- [LE10377AA](#)
- [EMDX3 Energy Counter ModbusTable LG EN](#)

Installation instructions & related documents

- [LE10376AC](#)