

CAT. N° 4 121 25



**SINGLE PHASE CURRENT TRANSFORMER (CT) FOR  
40.5X12.5 / 32.5X20.5 MM BAR - TRANSFORMATION RATIO  
400/5**

|                           |        |
|---------------------------|--------|
| Pack (number of units)    | 1      |
| Volume (dm <sup>3</sup> ) | 0,655  |
| Weight (g)                | 393,00 |

Product characteristics

**Single-phase solid core current transformers**

- Used with ammeters, electricity meters or multi-function measuring units
- Current at the secondary: 5 A
- Can be fixed on plate, EN 60715 rail Cat.No 4 121 01/02/03/04/05/06/07, or bars
- Secondary connected by terminals or lugs
- Precision class: 1 %


**For 40,5 x 10,5, 32,5 x 20,5 and 25,5 x 25,5 mm bars or Ø32 mm cable**

- Transformation ratio : 400/5
- Output : 8 VA

General characteristics

**Current transformers (CT)**

Documentation

 **Catalogue pages & additional information**

- [Description page \(p.106\)](#)
- [Current transformers \(CT\)](#)

 **Installation & technical data**

- [F01960EN-02](#)