

CAT. N° 4 121 38

**SINGLE PHASE CURRENT TRANSFORMER (CT) FOR 65 X 32 MM BAR - TRANSFORMATION RATIO 800/5**


|                           |        |
|---------------------------|--------|
| Pack (number of units)    | 1      |
| Volume (dm <sup>3</sup> ) | 1,425  |
| Weight (g)                | 513,00 |

**Product characteristics****Single-phase solid core current transformers**

- Used with ammeters, electricity meters or multi-function measuring units
- Current at the secondary: 5 A
- Can be fixed on plate, EN 60715 rail Cat.No 4 121 01/02/03/04/05/06/07, or bars
- Secondary connected by terminals or lugs
- Precision class: 1 %

**For 65 x 32 mm bar**

- Transformation ratio : 800/5
- Output : 12 VA

**General characteristics****Current transformers (CT)****Documentation** **Catalogue pages & additional information**

- [Description page \(p.106\)](#)
- [Current transformers \(CT\)](#)

 **Installation & technical data**

- F01960EN-02