

CAT. N° 4 122 20


SPD - T2 - IMAX 20 KA/POLE - 1P

Pack (number of units)	1
Volume (dm ³)	0,198
Weight (g)	103,00

Product characteristics
T2 SPDs


- SPDs with plug-in modules and status indicators:
 - Green: SPD operational
 - Orange: plug-in modules to be replaced

T2 - I_{max} 20 kA/pole

- SPDs recommended for small installations
- Up: 1.2 kV - In: 5 kA/pole - Uc: 320 V~
- Earthing systems : TT, TNC, TNS
- Recommended MCB: DX³ 20 A - C curve
- Number of poles : 1P
- Remote status monitoring (FS contact) : No
- Number of modules : 1

General characteristics
Class II (T2) low voltage SPDs

- Protection against transient overvoltages for 230/400 V~ power networks (50/60 Hz). SPDs compliant with EN/IEC 61643-11 standards
- Recommended for distribution boards

Documentation
 **Catalogue pages & additional information**

- [Technical page \(p.074-075\)](#)
- [Description page \(p.077\)](#)
- [Technical page \(p.079\)](#)
- [Technical page \(p.080-081\)](#)
- [Dimensions of din-rail equipment](#)

 **Installation & technical data**

- [F02060EN_05](#)

 **Installation instructions & related documents**

- [LE07561AA_6](#)

 **Agreements & certificates of conformity**

- [OC / CB - AT 4283](#)