

CAT. N° 4 122 24



## SPD - T2 - IMAX 20 KA/POLE - 1P+N - NEUTRAL ON LEFT HAND SIDE

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,369
Weight (g)	181,00

### Product characteristics

#### T2 SPDs

- SPDs with plug-in modules and status indicators:
  - Green: SPD operational
  - Orange: plug-in modules to be replaced

#### T2 - I<sub>max</sub> 20 kA/pole

- SPDs recommended for small installations
- Up: 1.2 kV - In: 5 kA/pole - Uc: 320 V~
- Earthing systems : TT, TNC, TNS
- Recommended MCB: DX<sup>3</sup> 20 A - C curve
- 1P+N and 3P+N: L-N and N-PE protection modes (common and differential modes), the N pole being protected by encapsulated spark gaps. Also called 1+1 and 3+1
- Number of poles : 1P+N
- Neutral position : Left
- Remote status monitoring (FS contact) : No
- Number of modules : 2

### General characteristics

#### Class II (T2) low voltage SPDs

- Protection against transient overvoltages for 230/400 V~ power networks (50/60 Hz). SPDs compliant with EN/IEC 61643-11 standards
- Recommended for distribution boards

### Documentation

#### Catalogue pages & additional information

- [Technical page \(p.074-075\)](#)
- [Description page \(p.077\)](#)
- [Technical page \(p.079\)](#)
- [Technical page \(p.080-081\)](#)
- [Dimensions of din-rail equipment](#)

#### Installation & technical data

- [F02060EN\\_05](#)

#### Installation instructions & related documents

- [LE07561AA\\_6](#)

#### Agreements & certificates of conformity

- [OC / CB - AT 4283](#)