

CAT. N° 4 122 41


**SPD - T2 - IMAX 40 KA/POLE - 2P**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,369
Weight (g)	213,00

**Product characteristics**
**T2 SPDs**


- SPDs with plug-in modules and status indicators:
  - Green: SPD operational
  - Orange: plug-in modules to be replaced

**T2 - I<sub>max</sub> 40 kA/pole**

- SPDs recommended for power installations
- Up: 1.7 kV - In: 20 kA/pole - Uc: 320 V~
- Earthing systems : TT, TNC, TNS
- Recommended MCB: DX<sup>3</sup> 25 A - C curve
- Number of poles : 2P
- Remote status monitoring (FS contact) : No
- Number of modules : 2

**General characteristics**
**Class II (T2) low voltage SPDs**

- Protection against transient overvoltages for 230/400 V~ power networks (50/60 Hz). SPDs compliant with EN/IEC 61643-11 standards
- Recommended for distribution boards

**Documentation**
 **Catalogue pages & additional information**

- [Technical page \(p.074-075\)](#)
- [Description page \(p.077\)](#)
- [Technical page \(p.079\)](#)
- [Technical page \(p.080-081\)](#)
- [Dimensions of din-rail equipment](#)

 **Installation & technical data**

- [F02060EN\\_05](#)

 **Installation instructions & related documents**

- [LE07561AA\\_6](#)

 **Agreements & certificates of conformity**

- [OC / CB - AT 4283](#)