

CAT. N° 4 125 03


**POWER CONTACTOR CX<sup>3</sup> - WITH 24 V~ COLL - 2P 250 V~  
-16 A - N/C+N/O**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,211
Weight (g)	129,00

**Product characteristics**
**Power contactors with 24 V~ coil**
**2-pole - 250 V~**

- I max : 16 A
- Type of contact : N/C + N/O
- Number of modules : 1

**General characteristics**
**Power contactors without handle CX<sup>3</sup> - from 16 A to 63 A**

- Conform to IEC/EN 61095
- Space for power supply busbar on top (up to 25 A)

**Documentation**

**Catalogue pages & additional information**

- [Description page \(p.087\)](#)
- [Technical page \(p.088\)](#)
- [Dimensions of din-rail equipment](#)


**Agreements & certificates of conformity**

- [NF-NF012\\_2632](#)
- [VDE-40029913](#)
- [OC / CB-CB\\_FR\\_709436](#)


**Installation & technical data**

- [F01332EN-03](#)


**Environmental product profile**

- [Environnemental product sheet n°8 E0007B-FR](#)
- [LGRP-00980-V02](#)
- [LGRP-2015-302-v1-EN](#)