

CAT. N° 4 125 09


**POWER CONTACTOR CX<sup>3</sup> - WITH 24 V~ COLL - 4P 400 V~  
-25 A - 2 N/C+ 2 N/O**


Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,369
Weight (g)	234,00

**Product characteristics**
**Power contactors with 24 V~ coil**
**4-pole - 400 V~**

- I max : 25 A
- Type of contact : 2 N/C + 2 N/O
- Number of modules : 2

**General characteristics**
**Power contactors without handle CX<sup>3</sup> - from 16 A to 63 A**

- Conform to IEC/EN 61095
- Space for power supply busbar on top (up to 25 A)

**Documentation**
 **Catalogue pages & additional information**

- [Description page \(p.087\)](#)
- [Technical page \(p.088\)](#)
- [Dimensions of din-rail equipment](#)

 **Agreements & certificates of conformity**

- [NF - NF012\\_2632](#)
- [OC / CB - FR\\_709436](#)
- [VDE - 40029913](#)

 **Installation & technical data**

- [F01332EN-03](#)

 **Environmental product profile**

- [Environnemental product sheet n°8 E0008B-FR](#)