

CAT. N° 4 126 02


TIME-LAG SWITCH - 16 A 230 V~ - 50/60 HZ - 1 MODULE


Pack (number of units)	10
Volume (dm ³)	2,238
Weight (g)	871,00

Product characteristics
Time-lag switch

- Resettable
- 230 V~ - 50/60 Hz
- Timing adjustable from 0.5 sec to 10 min
- Manual override contact
- Output 16 A - 250 V~ - ? cos ? = 1
- 2000 W incandescent/halogen
- 2000 W halogen - 230 V~
- 1000 VA fluo - series compensated
- 120 VA fluo - parallel compensated 14 ?F
- 100 VA compact fluorescent
- 1000 W energy saving lamp automatic 3-wire or 4-wire connection
- Number of modules : 1

General characteristics
Electronic time-lag switches

- Designed for supply busbar compatibility
- Power supply: 230 V~ - 50/60 Hz
- Switches a lighting circuit for a specific time
- Self-protection in the event of blocked pushbutton

Documentation
 **Catalogue pages & additional information**

- [Description page \(p.093\)](#)
- [Dimensions of din-rail equipment](#)

 **Agreements & certificates of conformity**

- [VDE-40013008](#)

 **Installation instructions & related documents**

- [292552-02](#)

 **Environmental product profile**

- [LGRP-00679-V01](#)