

CAT. N° 4 126 23



## LIGHT SENSITIVE SWITCH - STANDARD - OUTPUT 16 A 250 V~

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,677
Weight (g)	155,00

### Product characteristics

#### Standard

- Output 16 A - 250 V~ -  $\mu \cos \varphi = 1$
- 2000 W incandescent
- 2000 W series compensated fluorescent
- 1000 W parallel compensated fluorescent 70  $\mu$ F
- 1000 W energy-saving bulb
- 2000 W halogen bulb + ferromagnetic transformer
- 2000 W halogen bulb + electronic transformer
- Automatic timer response
- Adjustable from 1 to 100 000 lux
- Number of modules: 1
- Supplied with IP 65 photoelectric cell Cat.No 4 128 60

### General characteristics

#### Light sensitive switches

- Can be used to switch a lighting circuit "ON" and "OFF" based on light conditions (nightfall, daybreak)
- Supplied with IP 65 weatherproof photoelectric cell
- Power supply: 230 V~ - 50/60 Hz

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.094\)](#)
- [Dimensions of din-rail equipment](#)
- [Light sensitive switches](#)



#### Agreements & certificates of conformity

- [VDE - 40032903](#)



#### Installation instructions & related documents

- [292533-05](#)