

CAT. N° 4 126 33



## PROGRAMMABLE TIME SWITCH DIGITAL DISP. -24 V~ -MULTIFUNCTION 56 PROG. -1 OUTPUT

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,451
Weight (g)	187,00

### Product characteristics

#### Multiple functions - daily or weekly programme - 5 years clock working reserve

- Programme settings: on daily or weekly basis 15 languages
- A programme consists of a on and off time and their assignment to certain days
- Option to suspend the programme for a specific period to set-up with start and date
- Minimum programme setting: 1 s.
- High precision clock:  $\pm 0.1$  sec per day
- Particularly suited to irregular cycles:
  - security installations (access point, alarms, etc.),
  - industrial installations (pump stations, etc.)
- Programmed directly on keypad, or using program transfer key Cat.No 4 128 72
- Additional functions including random (irregular cycles), hour counters

#### Power supply 24 V~ - 50/60 Hz and =

- 1 output 16 A - 24 V~
- 56 programmes
- $\mu \cos \varphi = 1$  per 1 inverter contact
- Number of modules : 2

### General characteristics

#### Programmable time switches - with digital display

- For switching an electric circuit (lighting, heating) ON or OFF at selected times during a pre-programmed time period
- Temporary (automatic return) or permanent (forced switching ON or OFF) override on output

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.090\)](#)
- [Technical page \(p.091\)](#)
- [Dimensions of din-rail equipment](#)

#### Agreements & certificates of conformity

- [VDE - 40035703](#)

#### Installation instructions & related documents

- [292555GB-03](#)