

CAT. N° 4 159 56

**DX³ STOP ARC 10000 WITH BOTTOM SIDE SUPPLY - 1P+N ON RIGHT-HAND SIDE - 30 MA - A TYPE 230 V~ - 10 A - 3 MODULES -B CURVE**

Pack (number of units)	1
Volume (dm ³)	0,521
Weight (g)	331,00

Product characteristics**Arc fault detection residual current circuit breakers**

- Breaking capacity:
 - 10000 - IEC 61009-1 - 230/240 V~
- Compatible with both prong-type and fork type supply busbars

Single pole + neutral 230 V~ A Type 30 mA

- Neutral on right-hand side
- B curve
- Nominal rating I_n : 10 A
- Number of modules : 3

General characteristics**DX³ Stop Arc - bottom side supply - arc fault detection devices from 10 to 20 A**

- Conform to IEC/EN 62606
- Can be equipped with DX³ signalling and remote tripping auxiliaries
- Specific use: fire prevention by arc detection

Documentation**Catalogue pages & additional information**

- [Description page \(p.063\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)