

CAT. N° 4 159 64

**DX<sup>3</sup> STOP ARC 10000 WITH BOTTOM SIDE SUPPLY - 1P+N  
ON RIGHT-HAND SIDE - 30 MA - A TYPE 230 V~ - 6A - 3  
MODULES -C CURVE**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,521
Weight (g)	331,00

**Product characteristics****Arc fault detection residual current circuit breakers**

- Breaking capacity:
  - 10000 - IEC 61009-1 - 230/240 V~
- Compatible with both prong-type and fork type supply busbars

**Single pole + neutral 230 V~ A Type 30 mA**

- Neutral on right-hand side
- Nominal rating I<sub>n</sub> : 6 A
- Number of modules : 3

**General characteristics****DX<sup>3</sup> Stop Arc - bottom side supply - arc fault  
detection devices from 10 to 20 A**

- Conform to IEC/EN 62606
- Can be equipped with DX<sup>3</sup> signalling and remote tripping auxiliaries
- Specific use: fire prevention by arc detection

**Documentation****Catalogue pages & additional information**

- [Description page \(p.063\)](#)