

CAT. N° 4 159 65



## DX<sup>3</sup> STOP ARC 10000 WITH BOTTOM SIDE SUPPLY - 1P+N ON RIGHT-HAND SIDE - 30 MA - A TYPE 230 V~ - 10 A - 3 MODULES - C CURVE

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,521
Weight (g)	328,00

### Product characteristics

#### Arc fault detection residual current circuit breakers

- Breaking capacity:
  - 10000 - IEC 61009-1 - 230/240 V~
  - Compatible with both prong-type and fork type supply busbars

#### Single pole + neutral 230 V~ A Type 30 mA

- Neutral on right-hand side
- C curve
- Nominal rating I<sub>n</sub> : 10 A
- Number of modules : 3

### General characteristics

#### DX<sup>3</sup> Stop Arc - bottom side supply - arc fault detection devices from 10 to 20 A

- Conform to IEC/EN 62606
- Can be equipped with DX<sup>3</sup> signalling and remote tripping auxiliaries
- Specific use: fire prevention by arc detection

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.063\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

#### Installation & technical data

- [F02546EN-04](#)

#### Video

- [DX3-StopArc\\_EN\\_N\\_RIGHT](#)

#### Installation instructions & related documents

- [LE10543BD](#)

#### Documents & videos

- [DX3-StopArc\\_EN\\_N\\_RIGHT](#)