

CAT. N° 4 166 51

**THERMAL OVERLOAD RELAY RTX<sup>3</sup> 40 - 7 TO 10 A - FOR CTX<sup>3</sup> 22 AND 40 - NON DIFF.**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,372
Weight (g)	182,00

**Product characteristics****Thermal overload relays**


- Class 10A
- Integrated auxiliary contacts 1 NO + 1 NC

**RTX<sup>3</sup> 40**

- For CTX<sup>3</sup> 22 and 40
- With screw terminals
- Type standard
- Adjustment range - I min. : 7 A
- Adjustment range - I max. : 10 A

**General characteristics****Thermal relays RTX<sup>3</sup> - for CTX<sup>3</sup> 3-pole industrial contactors**

- Thermal protection against overloads, long starting times and lasting stalling of the motor
- Differential type ensures a better protection in case of one phase failure thanks to faster tripping
- Conform to IEC 60 947-1, IEC 60 947-4-1

**Documentation**** Catalogue pages & additional information**

- [Description page \(p.192\)](#)
- [Technical page \(p.186-187\)](#)
- [Technical page \(p.196-197\)](#)
- [Thermal relays RTX<sup>3</sup> - screw type terminals](#)