

CAT. N° 4 173 14



MPCB MPX³ 32S - THERMAL MAGNETIC - MOTOR PROTECTION - 3P - 26 A - 15 KA

| | |
|---------------------------|--------|
| Pack (number of units) | 1 |
| Volume (dm ³) | 0,499 |
| Weight (g) | 325,00 |

Product characteristics

Thermal magnetic MPCBs

- Adjustable thermal release
- Magnetic release 13 le max.

MPX³ 32S

- Standard breaking capacity
- With toggle handle
- Fixing on rail
- 3-phase motor 400/415 V : 11 kW
- Thermal release adjustment range : 18 to 26 A
- Magnetic release operating current : 338 A
- 415 V breaking capacity Icu : 15 kA

General characteristics

MPCBs MPX³ - motor protection circuit breakers from 0.16 A to 100 A

- Conform to IEC 60947-1, IEC 60947-2, IEC 60947-4 ; class 10

Documentation



Catalogue pages & additional information

- [Description page \(p.184\)](#)
- [Technical page \(p.182-183\)](#)
- [MPCBs MPX3](#)



Installation & technical data

- [F01988EN-05](#)



Installation instructions & related documents

- [LE07207AB](#)



Environmental product profile

- [Environnemental product sheet n°8 E0083A-EN](#)