

REF . 4 173 15



MPCB MPX³ 32S - THERMAL MAGNETIC - MOTOR PROTECTION - 3P - 32 A - 15 KA



Emballage (nombre number of units)	1
Volume (dm ³)	0,499
Poids (g)	325,00

Caractéristiques du produit

Thermal magnetic MPCBs

- Adjustable thermal release
- Magnetic release 13 le max.

MPX³ 32S

- Standard breaking capacity
- With toggle handle
- Fixing on rail
- 3-phase motor 400/415 V : 15 kW
- Thermal release adjustment range : 22 to 32 A
- Magnetic release operating current : 416 A
- 415 V breaking capacity Icu : 15 kA

Caractéristiques générales

MPCBs MPX³ - motor protection circuit breakers from 0.16 A to 100 A

- Conform to IEC 60947-1, IEC 60947-2, IEC 60947-4 ; class 10

Documentation associée



Catalogue pages & additional information

- [Technical page \(p.182-183\)](#)
- [Description page \(p.184\)](#)
- [MPCBs MPX3](#)



Installation & technical data

- [F01988EN-05](#)



Installation instructions & related documents

- [LE07207AB](#)



Environmental product profile

- [LGRP-00211-V01](#)