

REF . 4 173 26


MPCB MPX³ 32H - THERMAL MAGNETIC - MOTOR PROTECTION - 3P - 2.5 A - 100 KA


Emballage (nombre number of units)	1
Volume (dm ³)	0,524
Poids (g)	372,00

Caractéristiques du produit
Thermal magnetic MPCBs

- Adjustable thermal release
- Magnetic release 13 le max.

MPX³ 32H

- High breaking capacity
- With rotary handle
- Fixing on rail
- 3-phase motor 400/415 V : 0.75 kW
- Thermal release adjustment range : 1.6 to 2.5 A
- Magnetic release operating current : 32.5 A
- 415 V breaking capacity Icu : 100 kA

Caractéristiques générales
MPCBs MPX³ - motor protection circuit breakers from 0.16 A to 100 A

- Conform to IEC 60947-1, IEC 60947-2, IEC 60947-4 ; class 10

Documentation associée

Catalogue pages & additional information

- [Technical page \(p.182-183\)](#)
- [Description page \(p.184\)](#)
- [MPCBs MPX3](#)


Installation & technical data

- [F01988EN-05](#)


Installation instructions & related documents

- [LE07207AB](#)


Environmental product profile

- [LGRP-00211-V01](#)