

CAT. N° 4 173 40



## MPCB MPX<sup>3</sup> 32 MA - MAGNETIC - MOTOR PROTECTION - 3P - 0.16 A - 100 KA

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,524
Weight (g)	357,00

### Product characteristics

#### Magnetic only MPCBs

- Without thermal release
- Magnetic release 13 x I<sub>e</sub> max.

#### MPX<sup>3</sup> 32MA

- High breaking capacity
- With rotary handle
- Fixing on rail
- 3P
- 3-phase motor 400/415 V : 0.02 kW
- Magnetic release operating current : 2.1 A
- 415 V breaking capacity I<sub>cu</sub> : 100 kA

### General characteristics

#### MPCBs MPX<sup>3</sup> - motor protection circuit breakers from 0.16 A to 100 A

- Conform to IEC 60947-1, IEC 60947-2, IEC 60947-4 ; class 10

### Documentation



#### Catalogue pages & additional information

- [Technical page \(p.182-183\)](#)
- [Description page \(p.184\)](#)
- [MPCBs MPX3](#)



#### Installation & technical data

- [F01988EN-05](#)



#### Installation instructions & related documents

- [LE07207AB](#)