

CAT. N° 4 173 46



MPCB MPX³ 32 MA - MAGNETIC - MOTOR PROTECTION - 3P - 2.5 A - 100 KA

Pack (number of units)	1
Volume (dm ³)	0,534
Weight (g)	367,00

Product characteristics

Magnetic only MPCBs

- Without thermal release
- Magnetic release $13 \times I_e$ max.

MPX³ 32MA

- High breaking capacity
- With rotary handle
- Fixing on rail
- 3P
- 3-phase motor 400/415 V : 0.75 kW
- Magnetic release operating current : 32.5 A
- 415 V breaking capacity I_{cu} : 100 kA

General characteristics

MPCBs MPX³ - motor protection circuit breakers from 0.16 A to 100 A

- Conform to IEC 60947-1, IEC 60947-2, IEC 60947-4 ; class 10

Documentation



Catalogue pages & additional information

- [Technical page \(p.182-183\)](#)
- [Description page \(p.184\)](#)
- [MPCBs MPX3](#)



Installation & technical data

- [F01988EN-05](#)



Installation instructions & related documents

- [LE07207AB](#)



Environmental product profile

- [LGRP-00211-V01](#)