

CAT. N° 4 173 63



MPCB MPX³ 63H - THERMAL MAGNETIC - MOTOR PROTECTION - 3P - 22 A - 50 KA

Pack (number of units)	1
Volume (dm ³)	1,435
Weight (g)	1 016,00

Product characteristics

Thermal magnetic MPCBs

- Adjustable thermal release
- Magnetic release 13 Ie max.

MPX³ 63H

- High breaking capacity
- With rotary handle
- Fixing on rail or by screw
- 3-phase motor 400/415 V : 7.5 kW
- Thermal release adjustment range : 14 to 22 A
- Magnetic release operating current : 286 A
- 415 V breaking capacity Icu : 50 kA

General characteristics

MPCBs MPX³ - motor protection circuit breakers from 0.16 A to 100 A

- Conform to IEC 60947-1, IEC 60947-2, IEC 60947-4 ; class 10

Documentation

Catalogue pages & additional information

- [Technical page \(p.182-183\)](#)
- [Description page \(p.184\)](#)
- [MPCBs MPX3](#)

Installation & technical data

- [F01988EN-05](#)

Installation instructions & related documents

- [LE07207AB](#)

Environmental product profile

- [LGRP-00211-V01](#)