

CAT. N° 4 173 70



MPCB MPX³ 100H - THERMAL MAGNETIC - MOTOR PROTECTION - 3P - 17 A - 100 KA

| | |
|---------------------------|----------|
| Pack (number of units) | 1 |
| Volume (dm ³) | 2,384 |
| Weight (g) | 2 232,00 |

Product characteristics

Thermal magnetic MPCBs

- Adjustable thermal release
- Magnetic release 13 Ie max.

MPX³ 100H

- High breaking capacity
- With rotary handle
- Fixing on rail or by screw
- 3P
- 3-phase motor 400/415 V : 7.5 kW
- Thermal release adjustment range : 11 to 17 A
- Magnetic release operating current : 221 A
- 415 V breaking capacity Icu : 100 kA

General characteristics

MPCBs MPX³ - motor protection circuit breakers from 0.16 A to 100 A

- Conform to IEC 60947-1, IEC 60947-2, IEC 60947-4 ; class 10

Documentation

Catalogue pages & additional information

- [Technical page \(p.182-183\)](#)
- [Description page \(p.184\)](#)
- [MPCBs MPX3](#)

Installation & technical data

- F01988EN-05

Installation instructions & related documents

- LE07207AB

Environmental product profile

- LGRP-00211-V01