

CAT. N° 4 173 74



MPCB MPX³ 100H - THERMAL MAGNETIC - MOTOR PROTECTION - 3P - 40 A - 100 KA

| | |
|---------------------------|----------|
| Pack (number of units) | 1 |
| Volume (dm ³) | 2,326 |
| Weight (g) | 2 275,00 |

Product characteristics

Thermal magnetic MPCBs

- Adjustable thermal release
- Magnetic release 13 Ie max.

MPX³ 100H

- High breaking capacity
- With rotary handle
- Fixing on rail or by screw
- 3P
- 3-phase motor 400/415 V : 18.5 kW
- Thermal release adjustment range : 28 to 40 A
- Magnetic release operating current : 520 A
- 415 V breaking capacity Icu : 100 kA

General characteristics

MPCBs MPX³ - motor protection circuit breakers from 0.16 A to 100 A

- Conform to IEC 60947-1, IEC 60947-2, IEC 60947-4 ; class 10

Documentation



Catalogue pages & additional information

- [Technical page \(p.182-183\)](#)
- [Description page \(p.184\)](#)
- [MPCBs MPX3](#)



Installation & technical data

- F01988EN-05



Installation instructions & related documents

- [LE07207AB](#)



Environmental product profile

- [Environnemental product sheet n°8 E0083A-EN](#)