

CAT. N° 4 189 29



RCBO - DX³ 10000 WITH BLACK NEUTRAL LEAD - 1P 230 V~ - 32 A - 10 MA - A TYPE - C CURVE

Pack (number of units)	O/R
Volume (dm ³)	O/R
Weight (g)	O/R

Product characteristics

Single pole - 230 V~

A Type 10 mA

- C curve
- Nominal rating In : 32 A
- Number of modules : 1

General characteristics

RCBOs DX³ 10000 - black neutral lead - residual circuit breakers from 6 to 40 A - A type

- Conform to IEC 61009-1 and BS/NZS 61009-1
- Compatible with both prong-type and fork type supply busbars
- Voltage dependent tripping
- Breaking capacity:
 - 10000 - IEC 61009-1
- A type : detect AC and DC component faults
- Solid neutral (not switched)
- Functional earth (FE) cable ensuring RCD protection in case of neutral interruption
- Downstream connection top side
- Can be equipped with DX³ signalling and remote tripping auxiliaries and motorised controls

Documentation

Catalogue pages & additional information

- [Description page \(p.059\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

Installation & technical data

- [F02715EN-01](#)

Installation instructions & related documents

- [LE09935AB](#)

Agreements & certificates of conformity

- [IMQ - IT-20333](#)