

CAT. N° 4 189 41



## RCBO - DX<sup>3</sup> 10000 WITH BLACK NEUTRAL LEAD - 1P 230 V~ - 10 A - 100 mA - A TYPE - C CURVE

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,477
Weight (g)	223,00

### Product characteristics

#### Single pole - 230 V~

#### A Type 100 mA

- C curve
- Nominal rating I<sub>n</sub> : 10 A
- Number of modules : 1

### General characteristics

#### RCBOs DX<sup>3</sup> 10000 - black neutral lead - residual circuit breakers from 6 to 40 A - A type

- Conform to IEC 61009-1 and BS/NZS 61009-1
- Compatible with both prong-type and fork type supply busbars
- Voltage dependent tripping
- Breaking capacity:
  - 10000 - IEC 61009-1
- A type : detect AC and DC component faults
- Solid neutral (not switched)
- Functional earth (FE) cable ensuring RCD protection in case of neutral interruption
- Downstream connection top side
- Can be equipped with DX<sup>3</sup> signalling and remote tripping auxiliaries and motorised controls

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.059\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

#### Installation & technical data

- [F02715EN-01](#)

#### Installation instructions & related documents

- [LE09935AB](#)

#### Agreements & certificates of conformity

- [OC / CB-IT-20333](#)