

CAT. N° 4 191 68



## MCB RX<sup>3</sup> 6000 - 3P 400 V~ - 13 A - B CURVE - PRONG/FORK TYPE SUPPLY BUSBARS

Pack (number of units)	4
Volume (dm <sup>3</sup> )	1,864
Weight (g)	1 522,00

### Product characteristics

#### 3-pole 400 V~

- B curve
- Nominal rating I<sub>n</sub> : 13 A
- Number of modules : 3

### General characteristics

#### MCBs RX<sup>3</sup> 6000 - thermal magnetic MCBs from 6 A to 63 A - B curve

- Conform to IEC 60898-1
- Do not accept auxiliaries, and add-on modules
- Compatible with prong-type and fork type supply busbars
- Breaking capacity:
  - 6000 - IEC 60898-1 - 230/400 V~
  - 6 kA - IEC 60947-2 - 230/400 V~
  - 10000 - IEC 60898-1 - 127/220 V~
  - 10 kA - IEC 60947-2 - 127/220 V~

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.052\)](#)
- [Dimensions of din-rail equipment](#)



#### Agreements & certificates of conformity

- [QC / CB - IT-14270](#)
- [VDE - 40041249](#)
- [IMQ - IT-14270](#)



#### Installation & technical data

- [F01909EN-02](#)