

CAT. N° 4 195 00



## MCB RX<sup>3</sup> 3000 - 1P+N 230 V~ - 20 A - C CURVE - NEUTRAL ON LEFT-HAND SIDE

Pack (number of units)	10
Volume (dm <sup>3</sup> )	1,633
Weight (g)	1 075,00

### Product characteristics

#### Single pole + neutral 230 V~ neutral on left-hand side

- C curve
- Nominal rating I<sub>n</sub> : 20 A
- Number of modules : 1

### General characteristics

#### MCBs RX<sup>3</sup> 3000 - thermal magnetic MCBs from 6 A to 32 A - C curve

- Conform to IEC 60898-1
- Do not accept auxiliaries, and RCD add-on modules
- Compatible with prong-type supply busbars
- Breaking capacity: 3000 - IEC 60898-1 - 230 V~

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.051\)](#)
- [Dimensions of din-rail equipment](#)

#### Agreements & certificates of conformity

- [QC / CB-670457](#)
- [NF-680926](#)

#### Installation & technical data

- [F02069EN-00](#)

#### Environmental product profile

- [LGRP-00358-V02](#)