

CAT. N° 4 195 01



MCB RX³ 3000 - 1P+N 230 V~ - 25 A - C CURVE - NEUTRAL ON LEFT-HAND SIDE

Pack (number of units)	10
Volume (dm ³)	1,633
Weight (g)	1 096,00

Product characteristics

Single pole + neutral 230 V~ neutral on left-hand side

- C curve
- Nominal rating I_n : 25 A
- Number of modules : 1

General characteristics

MCBs RX³ 3000 - thermal magnetic MCBs from 6 A to 32 A - C curve

- Conform to IEC 60898-1
- Do not accept auxiliaries, and RCD add-on modules
- Compatible with prong-type supply busbars
- Breaking capacity: 3000 - IEC 60898-1 - 230 V~

Documentation

Catalogue pages & additional information

- [Description page \(p.051\)](#)
- [Dimensions of din-rail equipment](#)

Agreements & certificates of conformity

- [QC / CB-670457](#)
- [NF-680926](#)

Installation & technical data

- [F02069EN-00](#)

Environmental product profile

- [LGRP-00358-V02](#)