

CAT. N° 4 196 94

**MCB RX<sup>3</sup> 4500 - 2P - 230/400 V~ - 6 A - C CURVE**

Pack (number of units)	6
Volume (dm <sup>3</sup> )	1,864
Weight (g)	1 562,00

**Product characteristics****2-pole 230/400 V~**

- C curve
- Nominal rating I<sub>n</sub> : 6 A
- Number of modules : 2

**General characteristics****MCBs RX<sup>3</sup> 4500 - thermal magnetic MCBs from 6 A to 63 A - C curve**

- Conform to IEC 60898-1
- Do not accept auxiliaries, and add-on modules
- Compatible with prong-type supply busbars
- Breaking capacity:
  - 4500 - IEC 60898-1 - 230/400 V~
  - 4.5 kA - IEC 60947-2 - 230/400 V~
  - 6000 - IEC 60898-1 - 127/220 V~
  - 6 kA - IEC 60947-2 - 127/220 V~

**Documentation****Catalogue pages & additional information**

- [Description page \(p.051\)](#)
- [Dimensions of din-rail equipment](#)

**Agreements & certificates of conformity**

- [OC / CB - IT 16504](#)
- [CEBEC - 20022](#)
- [VDE - 40042042](#)
- [VDE - 40044433](#)

**Installation & technical data**

- [F01911EN-01](#)