

CAT. N° 4 199 46

**MCB RX³ 4500 - 1P+N 230 V~ - 6 A - C CURVE - NEUTRAL ON LEFT-HAND SIDE**


Pack (number of units)	10
Volume (dm ³)	1,633
Weight (g)	1 049,00

Product characteristics**Single pole + neutral 230 V~ neutral on left-hand side**

- C curve
- Nominal rating In : 6 A
- Number of modules : 1

General characteristics**MCBs RX³ 4500 - thermal magnetic MCBs from 6 A to 63 A - C curve**

- Conform to IEC 60898-1
- Do not accept auxiliaries, and add-on modules
- Compatible with prong-type supply busbars
- Breaking capacity:
 - 4500 - IEC 60898-1 - 230/400 V~
 - 4.5 kA - IEC 60947-2 - 230/400 V~
 - 6000 - IEC 60898-1 - 127/220 V~
 - 6 kA - IEC 60947-2 - 127/220 V~

Documentation **Catalogue pages & additional information**

- [Description page \(p.051\)](#)
- [Dimensions of din-rail equipment](#)

 **Agreements & certificates of conformity**

- [QC / CB - 670457](#)

 **Installation & technical data**

- [F02068EN-00](#)

 **Environmental product profile**

- [Environnemental product sheet n°8 E0037C-EN](#)
- [Environnemental product sheet n°8 E0037C-EN](#)