

CAT. N° 4 200 06



MCCB THERMAL MAGNETIC - DPX³ 160 - ICU 16 KA 400 V~ - 3P - 125 A

Pack (number of units)	1
Volume (dm ³)	2,447
Weight (g)	1 270,00

Product characteristics

MCCBs - fixed version

- Thermal adjustable from 0,8 to 1 In
- Magnetic fixed at 10 In (fixed at 400 A for In 16 A and 25 A)

Breaking capacity Icu 16 kA (400 V~)

- 3P
- In : 125 A

General characteristics

DPX³ 160 thermal magnetic - MCCBs from 16 to 160 A

- Can be mounted on rail or on plate in XL³ cabinets and enclosures
- MCCBs for switching, control isolation and protection of low voltage electrical lines
- Supplied with fixing screws cage terminals 70 mm² max. (flexible cable) or 95 mm² max. rigid cable with accessories
- Can be fitted with DPX³ 160 and 250 common auxiliaries and accessories
- Conform to IEC 60947-2

Documentation

Catalogue pages & additional information

- [Description page \(p.136\)](#)
- [Technical page \(p.137\)](#)
- [Technical page \(p.143\)](#)
- [Technical page \(p.134-135\)](#)
- [DPX³ 160 & 250](#)
- [DPX³ 160/250/630 & 1600](#)

Installation & technical data

- [F01360EN03_DPX3160_MT_ENGv7](#)

Environmental product profile

- [Environnemental product sheet n°20 E0181B-EN](#)

Installation instructions & related documents

- [Y4220E](#)

Agreements & certificates of conformity

- [OC / CB - 71483](#)
- [OC / CB - 71479](#)