

CAT. N° 4 202 28



MCCB THERMAL MAGNETIC WITH E.L.C.B.S - DPX³ 250 - ICU 25 KA 400 V~ - 4P - 200 A

Pack (number of units)	1
Volume (dm ³)	4,371
Weight (g)	2 741,00

Product characteristics

MCCBs with electronic earth leakage module - fixed version

- Thermal adjustable from 0,8 to 1 In
- Magnetic adjustable from 5 to 10 In
- Equipped with earth leakage module with LCD screen
- Adjustable sensitivity: 0.03 - 0.3 - 1 - 3 A
- Adjustable tripping: 0 - 0.3 - 1 - 3s (with 0.03 A possible only 0s)

Breaking capacity Icu 25 kA (400 V~)

- 4P
- In : 200 A

General characteristics

DPX³ 250 thermal magnetic - MCCBs from 100 to 250 A

- Can be mounted on rail or on plate in XL³ cabinets and enclosures
- MCCBs for switching, control isolation and protection of low voltage electrical lines
- Supplied with fixing screws, connection plates for bars and cable lugs and insulated shields (phase barriers)
- Can be fitted with cage terminals 120 mm² max. (flexible cable) or 150 mm² max. rigid cable and with DPX³ 160 and 250 common auxiliaries and accessories
- Conform to IEC 60947-2

Documentation

Catalogue pages & additional information

- [Technical page \(p.134-135\)](#)
- [Description page \(p.138\)](#)
- [Technical page \(p.143\)](#)
- [DPX³ 160 & 250](#)
- [DPX³ 160/250/630 & 1600](#)

Installation & technical data

- [F01365EN03_DPX3250MT_RCD_ENG_v1](#)
- [DPX3250_Thermal_MagneticRCD4P_ModbusTable](#)
- [EXB16053_DPX3_160_250_EN](#)

Environmental product profile

- [LGRP-00451-V01](#)

Installation instructions & related documents

- [LE08865AB](#)
- [LE08866AB](#)
- [Y4263F](#)
- [Y4320C](#)

Agreements & certificates of conformity

- [OC / CB-67673](#)