

CAT. N° 4 202 38



## MCCB THERMAL MAGNETIC - DPX<sup>3</sup> 250 - ICU 36 KA 400 V~ - 3P - 200 A

Pack (number of units)	1
Volume (dm <sup>3</sup> )	2,829
Weight (g)	2 044,00

### Product characteristics

#### MCCBs - fixed version

- Thermal adjustable from 0,8 to 1 In
- Magnetic adjustable from 5 to 10 In

#### Breaking capacity I<sub>cu</sub> 36 kA (400 V~)

- 3P
- In : 200 A

### General characteristics

#### DPX<sup>3</sup> 250 thermal magnetic - MCCBs from 100 to 250 A

- Can be mounted on rail or on plate in XL<sup>3</sup> cabinets and enclosures
- MCCBs for switching, control isolation and protection of low voltage electrical lines
- Supplied with fixing screws, connection plates for bars and cable lugs and insulated shields (phase barriers)
- Can be fitted with cage terminals 120 mm<sup>2</sup> max. (flexible cable) or 150 mm<sup>2</sup> max. rigid cable and with DPX<sup>3</sup> 160 and 250 common auxiliaries and accessories
- Conform to IEC 60947-2

### Documentation

#### Catalogue pages & additional information

- [Technical page \(p.134-135\)](#)
- [Description page \(p.138\)](#)
- [Technical page \(p.143\)](#)
- [DPX<sup>3</sup> 160 & 250](#)
- [DPX<sup>3</sup> 160/250/630 & 1600](#)

#### Installation & technical data

- [F01364EN04\\_DPX3250MT\\_ENGV1](#)

#### Installation instructions & related documents

- [Y4263F](#)

#### Agreements & certificates of conformity

- [OC / CB - 71485](#)