

CAT. N° 4 202 78



MCCB THERMAL MAGNETIC - DPX³ 250 - ICU 50 KA 400 V~ - 4P - 200 A

Pack (number of units)	1
Volume (dm ³)	3,813
Weight (g)	2 596,00

Product characteristics

MCCBs - fixed version

- Thermal adjustable from 0,8 to 1 In
- Magnetic adjustable from 5 to 10 In

Breaking capacity Icu 50 kA (400 V~)

- 4P
- In : 200 A

General characteristics

DPX³ 250 thermal magnetic - MCCBs from 100 to 250 A

- Can be mounted on rail or on plate in XL³ cabinets and enclosures
- MCCBs for switching, control isolation and protection of low voltage electrical lines
- Supplied with fixing screws, connection plates for bars and cable lugs and insulated shields (phase barriers)
- Can be fitted with cage terminals 120 mm² max. (flexible cable) or 150 mm² max. rigid cable and with DPX³ 160 and 250 common auxiliaries and accessories
- Conform to IEC 60947-2

Documentation

Installation instructions & related documents

- [Y4263F](#)

Agreements & certificates of conformity

- [OC / CB-71485](#)

Installation & technical data

- [F01364EN04_DPX3250MT_ENGv1](#)
- [EXB16053_DPX3_160_250_EN](#)

Environmental product profile

- [LGRP-00570-V01](#)
- [LGRP-00733-V01](#)