

CAT. N° 4 202 98


**TRIP-FREE SWITCH - DPX<sup>3</sup>-I 250 - 4P WITH E.L.C.BS - 250 A**


Pack (number of units)	1
Volume (dm <sup>3</sup> )	4,371
Weight (g)	2 876,00

**Product characteristics**
**DPX<sup>3</sup>-I 250**

- 4P with earth leakage module
- Mounting on symmetrical rail with plate Cat.No 4 210 74
- In : 250 A

**General characteristics**
**DPX<sup>3</sup>-I trip-free switches - 160 to 1600 A**

- Trip-free switches for on-load circuit breaking and isolation of low voltage electrical circuits
- Can be associated to earth leakage modules or to corresponding DPX<sup>3</sup> residual current relays
- Conform to IEC 60947-3
- Category of use AC 23 A
- Connection identical to corresponding DPX<sup>3</sup>

**Documentation**
 **Catalogue pages & additional information**

- [Description page \(p.171\)](#)

 **Installation & technical data**

- [F01365EN03\\_DPX3250MT\\_RCD\\_ENG\\_v1](#)

 **Installation instructions & related documents**

- [Y4263F](#)
- [Y4320C](#)