

CAT. N° 4 203 72



## MCCB ELECTRONIC RELEASE - DPX<sup>3</sup> 250 - ICU 50 KA 400 V~ - 4P - 40 A

Pack (number of units)	1
Volume (dm <sup>3</sup> )	3,813
Weight (g)	2 456,00

### Product characteristics

#### MCCBs - fixed version

- Protection against overloads:
  - Ir adjustable from 0.4 to 1 x In
  - tr adjustable from 3 to 15s
- Protection against short circuits:
  - Isd adjustable from 1.5 to 10 x Ir
  - tsd adjustable from 0 to 0.5s

#### Breaking capacity Icu 50 kA (400 V~)

- 4P
- In : 40 A

### General characteristics

#### DPX<sup>3</sup> 250 electronic release - MCCBs from 40 to 250 A

- Can be mounted on rail or on plate in XL<sup>3</sup> cabinets and enclosures
- MCCBs for switching, control isolation and protection of low voltage electrical lines
- Supplied with fixing screws, connection plates for bars and cable lugs and insulated shields (phase barriers)
- Can be fitted with cage terminals 120 mm<sup>2</sup> max. (flexible cable) or 150 mm<sup>2</sup> max. rigid cable and with DPX<sup>3</sup> 160 and 250 common auxiliaries and accessories
- Conform to IEC 60947-2

### Documentation



#### Catalogue pages & additional information

- [Technical page \(p.134-135\)](#)
- [Description page \(p.139\)](#)
- [Technical page \(p.143\)](#)
- [DPX<sup>3</sup> 160 & 250](#)
- [DPX<sup>3</sup> 160/250/630 & 1600](#)