

CAT. N° 4 203 75



MCCB ELECTRONIC RELEASE - DPX³ 250 - Icu 50 KA 400 V~ - 4P - 100 A

Pack (number of units)	1
Volume (dm ³)	3,813
Weight (g)	2 456,00

Product characteristics

MCCBs - fixed version

- Protection against overloads:
 - Ir adjustable from 0.4 to 1 x In
 - tr adjustable from 3 to 15s
- Protection against short circuits:
 - Isd adjustable from 1.5 to 10 x Ir
 - tsd adjustable from 0 to 0.5s

Breaking capacity Icu 50 kA (400 V~)

- 4P
- In : 100 A

General characteristics

DPX³ 250 electronic release - MCCBs from 40 to 250 A

- Can be mounted on rail or on plate in XL³ cabinets and enclosures
- MCCBs for switching, control isolation and protection of low voltage electrical lines
- Supplied with fixing screws, connection plates for bars and cable lugs and insulated shields (phase barriers)
- Can be fitted with cage terminals 120 mm² max. (flexible cable) or 150 mm² max. rigid cable and with DPX³ 160 and 250 common auxiliaries and accessories
- Conform to IEC 60947-2

Documentation



Catalogue pages & additional information

- [Technical page \(p.134-135\)](#)
- [Description page \(p.139\)](#)
- [Technical page \(p.143\)](#)
- [DPX³ 160 & 250](#)
- [DPX³ 160/250/630 & 1600](#)



Installation & technical data

- [DPX3_250Electronic4P_ModbusTable](#)
- [F01362EN04_DPX3_250ELEENG_v1](#)
- [EXB20072_logic_selectivity \(print\)](#)
- [EXB16053_DPX3_160_250_EN](#)



Installation instructions & related documents

- [Y4268D](#)
- [Y4263E](#)



Agreements & certificates of conformity

- [OC / CB-67418A1](#)