

CAT. N° 4 220 01



## MCCB DPX<sup>3</sup> 630 - THERMAL MAGNETIC - 3P - ICU 36 KA (400 V~) - IN 320 A

Pack (number of units)	1
Volume (dm <sup>3</sup> )	8,91
Weight (g)	5 242,00

### Product characteristics

#### MCCBs thermal magnetic release - fixed version

- Thermal adjustable from 0.8 to 1 In
- Magnetic adjustable from 5 to 10 In

#### Breaking capacity Icu 36 kA (400 V~)

- 3P
- In : 320 A

### General characteristics

#### DPX<sup>3</sup> 630 - thermal magnetic release MCCBs from 250 to 630 A

- Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines
- Can be fitted with auxiliaries
- Can be used with earth leakage modules or with residual current relays
- Supplied complete with:
  - fixing screws
  - connection plates for bars
  - insulated shields (phase barriers)
- Conform to IEC 60947-2 - Sealable adjustment
- Can be mounted on plate in XL<sup>3</sup> cabinets and enclosures

### Documentation

#### Catalogue pages & additional information

- [Technical page \(p.134-135\)](#)
- [Description page \(p.144\)](#)
- [DPX<sup>3</sup> 160/250/630 & 1600](#)
- [DPX<sup>3</sup> 630](#)

#### Installation & technical data

- [F01958EN03 DPX3630\\_MT\\_ENG v1](#)
- [EXB19026\\_CA\\_DPX3\\_125HP250HP\\_630\\_1600EN](#)

#### Installation instructions & related documents

- [LE07062AB](#)

#### Environmental product profile

- [LGRP-00702-V01](#)