

CAT. N° 4 220 14



MCCB DPX³ 630 - THERMAL MAGNETIC - 3P - ICU 50 KA (400 V~) - IN 250 A

Pack (number of units)	1
Volume (dm ³)	10
Weight (g)	5 209,00

Product characteristics

MCCBs thermal magnetic release - fixed version

- Thermal adjustable from 0.8 to 1 In
- Magnetic adjustable from 5 to 10 In

Breaking capacity Icu 50 kA (400 V~)

- 3P
- In : 250 A

General characteristics

DPX³ 630 - thermal magnetic release MCCBs from 250 to 630 A

- Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines
- Can be fitted with auxiliaries
- Can be used with earth leakage modules or with residual current relays
- Supplied complete with:
 - fixing screws
 - connection plates for bars
 - insulated shields (phase barriers)
- Conform to IEC 60947-2 - Sealable adjustment
- Can be mounted on plate in XL³ cabinets and enclosures

Documentation



Catalogue pages & additional information

- [Description page \(p.144\)](#)
- [Technical page \(p.134-135\)](#)
- [DPX³ 160/250/630 & 1600](#)
- [DPX³ 630](#)



Environmental product profile

- [Environnemental product sheet n°20 E0170B-EN](#)