

CAT. N° 4 221 09

**MCCB DPX³ 630 - S2 ELEC RELEASE + CENTRAL - 3P - ICU
50 KA (400 V~) - IN 500 A**

Pack (number of units)	1
Volume (dm ³)	10
Weight (g)	5 953,00

Product characteristics**MCCBs electronic release S2 with energy metering central unit - fixed version**

- Adjustment of Ir, Isd, tr, tsd
- Instantaneous protection If = 5 kA
- Green indicator lamp
- Connector for test unit
- Logic and dynamic selectivity
- 4P version: adjustment of neutral on front panel

Breaking capacity Icu 50 kA (400 V~)

- 3P
- In : 500 A

General characteristics**DPX³ 630 - S2 electronic release MCCBs from 250 to 630 A**

- Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines
- Can be fitted with auxiliaries
- Can be used with earth leakage modules or with residual current relays
- Supplied complete with:
 - fixing screws
 - connection plates for bars
 - insulated shields (phase barriers)
- Conform to IEC 60947-2 - Sealable adjustment
- Can be mounted on plate in XL³ cabinets and enclosures

Documentation**Catalogue pages & additional information**

- [Description page \(p.146\)](#)
- [Technical page \(p.134-135\)](#)
- [DPX³ 160/250/630 & 1600](#)
- [DPX³ 630](#)

**Firmwares**

- [Legrand Power Control Station software](#)