

CAT. N° 4 221 12

**MCCB DPX<sup>3</sup> 630 - S2 ELEC RELEASE + CENTRAL - 4P - ICU  
50 KA (400 V~) - IN 320 A**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	10
Weight (g)	7 074,00

**Product characteristics****MCCBs electronic release S2 with energy metering central unit - fixed version**

- Adjustment of Ir, Isd, tr, tsd
- Instantaneous protection If = 5 kA
- Green indicator lamp
- Connector for test unit
- Logic and dynamic selectivity
- 4P version: adjustment of neutral on front panel

**Breaking capacity Icu 50 kA (400 V~)**

- 4P
- In : 320 A

**General characteristics****DPX<sup>3</sup> 630 - S2 electronic release MCCBs from 250 to 630 A**

- Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines
- Can be fitted with auxiliaries
- Can be used with earth leakage modules or with residual current relays
- Supplied complete with:
  - fixing screws
  - connection plates for bars
  - insulated shields (phase barriers)
- Conform to IEC 60947-2 - Sealable adjustment
- Can be mounted on plate in XL<sup>3</sup> cabinets and enclosures

**Documentation****Catalogue pages & additional information**

- [Description page \(p.146\)](#)
- [Technical page \(p.134-135\)](#)
- [DPX<sup>3</sup> 160/250/630 & 1600](#)
- [DPX<sup>3</sup> 630](#)

**Firmwares**

- [Legrand Power Control Station software](#)