

CAT. N° 4 221 18



## MCCB DPX<sup>3</sup> 630 - S2 ELEC RELEASE + CENTRAL - 3P - ICU 70 KA (400 V~) - IN 400 A

Pack (number of units)	1
Volume (dm <sup>3</sup> )	10
Weight (g)	5 640,00

### Product characteristics

#### MCCBs electronic release S2 with energy metering central unit - fixed version

- Adjustment of  $I_r$ ,  $I_{sd}$ ,  $t_r$ ,  $t_{sd}$
- Instantaneous protection  $I_f = 5$  kA
- Green indicator lamp
- Connector for test unit
- Logic and dynamic selectivity
- 4P version: adjustment of neutral on front panel

#### Breaking capacity Icu 70 kA (400 V~)

- 3P
- $I_n$  : 400 A

### General characteristics

#### DPX<sup>3</sup> 630 - S2 electronic release MCCBs from 250 to 630 A

- Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines
- Can be fitted with auxiliaries
- Can be used with earth leakage modules or with residual current relays
- Supplied complete with:
  - fixing screws
  - connection plates for bars
  - insulated shields (phase barriers)
- Conform to IEC 60947-2 - Sealable adjustment
- Can be mounted on plate in XL<sup>3</sup> cabinets and enclosures

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.146\)](#)
- [Technical page \(p.134-135\)](#)
- [DPX<sup>3</sup> 160/250/630 & 1600](#)
- [DPX<sup>3</sup> 630](#)

#### Installation & technical data

- [F01959EN02\\_DPX3\\_630ELE\\_ENG\\_v1\\_4](#)
- [ModbusTable\\_17](#)

#### Installation instructions & related documents

- [LE07061AA-02](#)
- [LE07062AA-03](#)
- [LE08865AB](#)
- [LE08866AB](#)

#### Firmwares

- [Legrand Power Control Station software](#)