

CAT. N° 4 221 40



MCCB DPX³ 630 - SG ELECTRONIC RELEASE - 3P - ICU 36 KA (400 V~) - IN 630 A

Pack (number of units)	1
Volume (dm ³)	10
Weight (g)	5 931,00

Product characteristics

MCCBs electronic release Sg - fixed version

- Adjustment of Ir, Isd, Ig, tr, tsd, tg
- Instantaneous protection If = 5 kA
- Green indicator lamp
- Connector for test unit
- Logic and dynamic selectivity
- 4P version: adjustment of neutral on front panel

Breaking capacity Icu 36 kA (400 V~)

- 3P
- In : 630 A

General characteristics

DPX³ 630 - Sg electronic release MCCBs from 250 to 630 A

- Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines
- Can be fitted with auxiliaries
- Can be used with earth leakage modules or with residual current relays
- Supplied complete with:
 - fixing screws
 - connection plates for bars
 - insulated shields (phase barriers)
- Conform to IEC 60947-2 - Sealable adjustment
- Can be mounted on plate in XL³ cabinets and enclosures

Documentation

Catalogue pages & additional information

- [Description page \(p.147\)](#)
- [Technical page \(p.134-135\)](#)
- [DPX³ 160/250/630 & 1600](#)
- [DPX³ 630](#)

Installation & technical data

- [F01959EN02_DPX3_630ELE_ENG_v1_4](#)
- [modbustable_20](#)

Installation instructions & related documents

- [LE07061AA-02](#)
- [LE07062AA-03](#)
- [LE08865AB](#)
- [LE08866AB](#)

Firmwares

- [Legrand Power Control Station software](#)