

CAT. N° 4 223 25



MCCB DPX³ 1600 - S2 ELECTRONIC RELEASE - 3P - ICU 70 KA (400 V~) - IN 1000 A

Pack (number of units)	1
Volume (dm ³)	48
Weight (g)	15 923,00

Product characteristics

MCCBs electronic release S2 fixed version

- Adjustment of Ir, Isd, tr, tsd
- Instantaneous protection If = 20 kA
- Green indicator lamp
- Connector for test unit
- Logic and dynamic selectivity

Breaking capacity Icu 70 kA (400 V~)

- 3P
- In : 1000 A

General characteristics

DPX³ 1600 - S2 electronic release MCCBs from 630 to 1600 A

- Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines
- Can be fitted with auxiliaries
- Can be used with residual current relays
- Supplied complete with:
 - connection plates for bars
 - insulated shields (phase barriers)
- Conform to IEC 60947-2 - Sealable adjustment
- Can be mounted on plate in XL³ cabinets and enclosures

Documentation

Catalogue pages & additional information

- [Technical page \(p.134-135\)](#)
- [Description page \(p.151\)](#)
- [DPX³ 160/250/630 & 1600](#)
- [DPX³ 1600](#)

Installation & technical data

- [F01964EN01](#)
- [ModbusTable_14](#)
- [EXB19026_CA_DPX3_125HP250HP_630_1600EN](#)
- [EXB20072_logic_selectivity \(print\)](#)

Installation instructions & related documents

- [LE07037AB](#)
- [LE07038AB](#)
- [LE08865AB](#)
- [LE08866AB](#)