

CAT. N° 4 225 67



MCCB DPX³ 1600 - S1 ELECTRONIC RELEASE - 3P - ICU 70 KA (400 V~) - IN 1600 A

Pack (number of units)	1
Volume (dm ³)	47,6
Weight (g)	16 875,00

Product characteristics

MCCBs electronic release S1 fixed version

- Adjustment of I_r , I_{sd}
- Instantaneous protection $I_f = 20$ kA
- Green indicator lamp
- Connector for test unit
- Dynamic selectivity
- 4P version: adjustment of neutral on front panel

Breaking capacity I_{cu} 70 kA (400 V~)

- 3P
- I_n : 1600 A

General characteristics

DPX³ 1600 - S1 electronic release MCCBs from 630 to 1600 A

- Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines
- Can be fitted with auxiliaries
- Can be used with residual current relays
- Do not accept DPX³ electronic interface for Modbus Cat.No 4 210 75
- Supplied complete with:
 - connection plates for bars
 - insulated shields (phase barriers)
- Conform to IEC 60947-2 - Sealable adjustment
- Can be mounted on plate in XL³ cabinets and enclosures

Documentation

Catalogue pages & additional information

- [Technical page \(p.134-135\)](#)
- [Description page \(p.150\)](#)
- [DPX³ 160/250/630 & 1600](#)
- [DPX³ 1600](#)

Installation & technical data

- [F01964EN01](#)
- [EXB19026_CA_DPX3_125HP250HP_630_1600EN](#)

Installation instructions & related documents

- [LE07037AB](#)
- [LE08011AA](#)