

CAT. N° 4 230 20

**DPX³250 HP THERMAL MAGNETIC RELEASE MCCB FIXED VERSION - BREAKING CAPACITY 36KA - 4P - 50A**

Pack (number of units)	1
Volume (dm ³)	4,232
Weight (g)	2 368,00

Product characteristics**MCCBs - fixed version**

- Thermal adjustable from 0.8 to 1 In
- Magnetic:
 - fixed at 400 A for In ≤ 40 A,
 - adjustable from 6.5 to 13 In for In = 50 A,
 - adjustable from 5 to 10 In for In ≥ 63 A

Breaking capacity Icu 36 kA (400 V~)

- 4P
- In : 50 A

General characteristics**DPX³ 250 HP - thermal magnetic release MCCBs from 16 to 250 A - fixing on plate**

- Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines
- Can be fitted with auxiliaries
- Supplied with: screws for connections, fixing screws, and insulated shileds (phase barriers)
- Can be fitted with cage terminals 120 mm² max. (flexible cable) or 150 mm² max. rigid cable
- Can be mounted on plate in XL³ and XL³ S cabinets and enclosures
- Conform to IEC 60947-2

Documentation **Installation instructions & related documents**

- [LE11440AB](#)

 **Environmental product profile**

- [LGRP-01375-V01](#)

 **Installation & technical data**

- [F03042EN03_DPX3250HP_TMv](#)