

REF . 4 232 22

**DPX³250 HP S1 ELECTRONIC RELEASE MCCB FIXED VERSION - BREAKING CAPACITY 50KA - 3P - 160A**

Emballage (nombre number of units)	1
Volume (dm ³)	3,276
Poids (g)	1 914,00

Caractéristiques du produit**MCCBs - fixed version**

- Protection against overloads:
 - Ir adjustable from 0.4 to 1 x In
 - tr adjustable from 3 to 15s
- Protection against short circuits:
 - I_{sd} adjustable from 1.5 to 10 x Ir
 - tsd adjustable from 0 to 0.5s

Breaking capacity I_{cu} 50 kA (400 V~)

- 3P
- In : 160 A

Caractéristiques générales**DPX³ 250 HP - S1 electronic release MCCBs from 40 to 250 A - fixing on plate**

- Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines
- Can be fitted with auxiliaries
- Supplied with: screws for connection fixing screws, connection plates for bars and cable lugs and insulated shileds (phase barriers)
- Can be fitted with cage terminals 120 mm² max. (flexible cable) or 150 mm² max. rigid cable
- Can be mounted on plate in XL³ and XL³ S cabinets and enclosures
- Conform to IEC 60947-2

Documentation associée** Installation instructions & related documents**

- [LE11682AA](#)

 Installation & technical data

- [F03044EN00_DPX3250_HPS1_ELEv](#)
- [EXB19026_CA_DPX3_125HP250HP_630_1600E](#)
N